



OPT CL1 Series Line Scan Cameras



OPT-CL1-M4-XG3-05


- 10GigE interface, provides up to 10Gbps effective bandwidth.
- Support ISP functions including FFC, Black level, LUT, Gamma etc.
- Support Software Trigger, Hardware Trigger, Free Run Mode.
- Support multiple image data formats output, ROI, Reverse, etc.
- Support DC12~24V wide-voltage power supply.
- Compatible with GigE Vision V2.0 Protocol, GenICam Standard, and third-party software based on these protocol and standard.

Specification


Model	Sensor type	Resolution	Line rate	Pixel size	Lens mount	Mono/Color
OPT-CL1-M4-XG3-05	CMOS	4096 × 1	200 kHz	7 μm × 7 μm	M42*1.0	Mono

Name	4K Mono 10GigE Line Scan Camera
Pixel format	Mono 8/10/10Packed/12/12Packed
Max. line rate	200 kHz@Mono 8
Dynamic range	61.5 dB
SNR	40.2 dB
Gain	1 dB ~ 15.5 dB
Exposure time	1 μs ~ 50 ms
Trigger mode	Internal Trigger, External Trigger
Binning	No Supports
Data interface	10 GigE
Power supply	12-pin Hirose interface power supply, Voltage range:12 ~ 24 VDC
Power consumption	13.56 W@24 VDC
Dimension	76 mm(W) × 76 mm(H) × 61.6 mm(D)
Weight	≈ 430 g
Temperature	Working temperature:0 ~ 50°C, Storage temperature:0 ~ 80°C
Operating system	Windows 7/10/11 32/64-bit, Linux 64-bit, MacOS 64bits
Compatibility	GigE Vision V2.0, GenICam
Certification	CE, RoHS, FCC


Spectral Response



Dimension (mm)



I/O Interface Description



PIN	Signal	Description
1	GND	Power ground
2	Power	DC 24V Camera Power Supply
3	EncoderA+	Encoder Differential signal Input A+
4	EncoderA-	Encoder Differential signal Input A-
5	EncoderB-	Encoder Differential signal Input B-
6	EncoderB+	Encoder Differential signal Input B+
7	OUT_GND	Opto-isolated Output ground
8	Lineout1	Opto-isolated Output 1
9	Lineout2	Opto-isolated Output 2
10	IN_GND	Opto-isolated Input ground
11	Line2	Opto-isolated Input 2
12	Line1	Opto-isolated Input 1



OPT MACHINE VISION TECH CO.,LTD.

No. 66 Xingfa South Road, Chang'an Town, Dongguan City, Guangdong Province, China
Tel: +86-769-82716188 Fax: +86-769-81606698
Email: optmv@optmv.com Web: www.optmv.net



Web



LinkedIn